

Specification Sheet

Part Number: 170-01163

Self-wrapping woven sleeving made of fiberglass and PET polyester protects against chewing damage.

Provides good protection against abrasion, UV and weathering, vibration and impact.

Quick and easy installation and removal, ideal for retrofitting.

Lightweight material won't add significant weight to the installation.

Resists acids, solvents and micro-organisms for extended performance in industrial environments.



Braided Sleeving, Twist-In Rodent-Repellent Wrap, 29mm Dia. FG/PET, White, 49.2 ft/rl

Article Number	170-01163
----------------	-----------

Type	Twist-In-RR-29
------	----------------

Color	Black (BK) White (WH)
-------	-----------------------

Quantity Per	pack
--------------	------

Product Description	Twist-In Rodent-Repellent Wrap is a self-closing fiberglass sleeving used to bundle cables and hoses and protect against rodents in infestation-prone areas such as automotive, railways, telecom, underground and waste treatment systems.
---------------------	---

Short Description	Braided Sleeving, Twist-In Rodent-Repellent Wrap, 29mm Dia. FG/PET, White, 49.2 ft/rl
Global Part Name	Twist-In-RR-29-PET/GF-BK/WH
Length L (Metric)	15
Bundle Diameter Min (Imperial)	0.98
Bundle Diameter Min (Metric)	25
Bundle Diameter Max (Imperial)	1.14
Bundle Diameter Max (Metric)	29
Nominal Diameter (Imperial)	1.0
Nominal Diameter (Metric)	25.4
Wall Thickness WT (Metric)	0.8
Material	Glass Fiber (GF) Polyester (PET)
Material Shortcut	GF PET
Flammability	FMVSS 302
Halogen Free	Yes

UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	EN [45545-2]
Package Quantity (Imperial)	49.2
Package Quantity (Metric)	15
Customs Number	7019901100

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com