

Specification Sheet

Part Number: 170-03015

Cuts with scissors without fraying ends enables field installations without need for hot knife.

Expands to 150% of easy installation and reduced assembly time requirements.

Material construction offers excellent abrasion and cut-through protection as well as inertness to common chemicals and fungus.



Braided Sleeve, Expandable, Fray Resistant, 1.25" Dia, PET, Black, 50 ft/reel

Article Number	170-03015
----------------	-----------

Type	BSPSC1140
------	-----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	A versatile and economical general purpose sleeving that resists fraying when cut with ordinary scissors. For use in automotive, industrial and computer applications where the wires, cables and hoses being covered endure frequent handling. It is suited for situations where access to a hot knife is either impractical or impossible.
---------------------	--

Short Description	Braided Sleeve, Expandable, Fray Resistant, 1.25" Dia, PET, Black, 50 ft/reel
-------------------	---

Global Part Name	BSPSC1140-PET-BK
------------------	------------------

Length L (Imperial)	50.0
---------------------	------

Length L (Metric)	15.2
-------------------	------

Bundle Diameter Min (Imperial)	1
--------------------------------	---

Bundle Diameter Min (Metric)	25.4
------------------------------	------

Bundle Diameter Max (Imperial)	1.5
--------------------------------	-----

Bundle Diameter Max (Metric)	38.1
------------------------------	------

Diameter D (Imperial)	1.25
-----------------------	------

Diameter D (Metric)	31.8
---------------------	------

Nominal Diameter (Imperial)	1.25
-----------------------------	------

Nominal Diameter (Metric)	31.8
---------------------------	------

Material	Polyester (PET)
----------	-----------------

Material Shortcut	PET
-------------------	-----

Flammability	UL 94 V-0
--------------	-----------

Halogen Free	Yes
--------------	-----

UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	15.24
Customs Number	5808100000

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com