

Specification Sheet

Part Number: 170-03034

HellermannTyton braided sleeving installation tools are designed to accommodate a wide variety of braided sleeving products.

Tools are designed and built durable to withstand production environments.

Tools are available in both benchmount and handheld for all kinds of use.



Braided Sleeving, Installation Tool, 1-1/4" Split Wrap, 1/pkg

Article Number	170-03034
----------------	-----------

Type	BSWTOOL114
------	------------

Color	Orange (OG)
-------	-------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton offers a wide variety of application tools to assist in the installation of braided sleeving. These application tools are available in both bench mount and handheld styles.
---------------------	--

Short Description	Braided Sleeving, Installation Tool, 1-1/4" Split Wrap, 1/pkg
-------------------	---

Global Part Name	BSWTOOL114-PL-OG
------------------	------------------

Bundle Diameter Max (Imperial)	1.25
Bundle Diameter Max (Metric)	31.8
Diameter D (Imperial)	1.25
Diameter D (Metric)	31.8
Nominal Diameter (Imperial)	1.25
Nominal Diameter (Metric)	31.8
Material	Plastic (PL)
Material Shortcut	PL
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)