

Specification Sheet

Part Number: 170-03039



Hot knife is designed and built durable to withstand production environments.

2.5" blades are replaceable.

Heats to 1,112 °F in 30 seconds.

110 volt operation.

Braided Sleeving, Bench Mount Hot Knife, 110 Volt Operation, 1/pkg

Article Number 170-03039

Type BSBHK

Color White (WH)

Quantity Per pack

Product Description For best results during sleeving installation, most braided sleeving should be cut with a hot knife.

Short Description Braided Sleeving, Bench Mount Hot Knife, 110 Volt Operation, 1/pkg

Global Part Name BSBHK-PL-WH

Material	Plastic (PL)
Material Shortcut	PL
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+1112°F (+600°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8515800080

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Privacy Policy](#)

[Cookie Policy](#)

[Terms and Conditions](#)