

Specification Sheet

Part Number: 170-03083



Split wrap design needs no fasteners and installs quickly, saving assembly time and future accessibility without disassembly.

Bends to a tight radius without distortion or splitting open.

Unique construction retains shape and rigidity throughout unrolling.

Easy open design allows quick access and ability to apply protective sleeving post assembly or post installation situations.

Braided Sleeving, Split Wrap, 0.5" Dia, PET, Orange, 150 ft/bulk reel

|                     |                                                                                                                                                                                                                                                                                                                                          |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 170-03083                                                                                                                                                                                                                                                                                                                                |
| Type                | BSPSW123B                                                                                                                                                                                                                                                                                                                                |
| Color               | Orange (OG), High Voltage (HV)                                                                                                                                                                                                                                                                                                           |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                                                     |
| Product Description | A lateral split semi-rigid braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires. |
| Short Description   | Braided Sleeving, Split Wrap, 0.5" Dia, PET, Orange, 150 ft/bulk reel                                                                                                                                                                                                                                                                    |

|                  |                  |
|------------------|------------------|
| Global Part Name | BSPSW123B-PET-OG |
|------------------|------------------|

|                     |       |
|---------------------|-------|
| Length L (Imperial) | 150.0 |
|---------------------|-------|

|                   |      |
|-------------------|------|
| Length L (Metric) | 45.7 |
|-------------------|------|

|                                |     |
|--------------------------------|-----|
| Bundle Diameter Min (Imperial) | 0.1 |
|--------------------------------|-----|

|                              |      |
|------------------------------|------|
| Bundle Diameter Min (Metric) | 2.54 |
|------------------------------|------|

|                                |     |
|--------------------------------|-----|
| Bundle Diameter Max (Imperial) | 0.5 |
|--------------------------------|-----|

|                              |      |
|------------------------------|------|
| Bundle Diameter Max (Metric) | 12.7 |
|------------------------------|------|

|                       |      |
|-----------------------|------|
| Diameter D (Imperial) | 0.50 |
|-----------------------|------|

|                     |      |
|---------------------|------|
| Diameter D (Metric) | 12.7 |
|---------------------|------|

|                             |     |
|-----------------------------|-----|
| Nominal Diameter (Imperial) | 0.5 |
|-----------------------------|-----|

|                           |      |
|---------------------------|------|
| Nominal Diameter (Metric) | 12.7 |
|---------------------------|------|

|                              |       |
|------------------------------|-------|
| Wall Thickness WT (Imperial) | 0.025 |
|------------------------------|-------|

|                            |      |
|----------------------------|------|
| Wall Thickness WT (Metric) | 0.64 |
|----------------------------|------|

|          |                 |
|----------|-----------------|
| Material | Polyester (PET) |
|----------|-----------------|

|                   |     |
|-------------------|-----|
| Material Shortcut | PET |
|-------------------|-----|

|                              |                                   |
|------------------------------|-----------------------------------|
| Flammability                 | UL 94 V-0                         |
| Halogen Free                 | Yes                               |
| UV Resistant (Yes/No)        | Yes                               |
| Use Conditions               | For Indoor and Outdoor Use        |
| Operating Temperature        | -94°F to +257°F (-70°C to +125°C) |
| Reach Compliant (Article 33) | Yes                               |
| ROHS Compliant               | Yes                               |
| UL Recognized (US)           | Yes                               |
| Package Quantity (Imperial)  | 150.0                             |
| Package Quantity (Metric)    | 45.7                              |
| Customs Number               | 5808100000                        |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com