

Specification Sheet

Part Number: 170-03097

A layer of aluminum provides protection from chemicals, scraping, cuts and abrasion.

Additional layer also provides insulation barrier for vulnerable wires and cables within high temperature environments.

Cuts with ordinary scissors for fast, easy application.



Braided Sleeving, Aluminum Laminated Fiberglass, 2.5" Dia, AL/GF, Silver, 50 ft/reel

Article Number 170-03097

Type BSHTTST212SR

Color Silver (SR)

Quantity Per pack

Product Description High Temperature Aluminum Laminated Fiberglass Sleeving is a tubular shaped product that combines the protection of bonded aluminum and fiberglass into a single solution that is able to reflect radiant heat away from the sensitive contents inside the tube.

Short Description Braided Sleeving, Aluminum Laminated Fiberglass, 2.5" Dia, AL/GF, Silver, 50 ft/reel

Global Part Name BSHTTST212SR-AL/GF-SR

| | |
|--------------------------------|--------------------------------|
| Length L (Imperial) | 50.0 |
| Length L (Metric) | 15.2 |
| Bundle Diameter Min (Imperial) | 0.1 |
| Bundle Diameter Min (Metric) | 2.54 |
| Bundle Diameter Max (Imperial) | 2.37 |
| Bundle Diameter Max (Metric) | 60.3 |
| Diameter D (Imperial) | 2.5 |
| Diameter D (Metric) | 63.5 |
| Nominal Diameter (Imperial) | 2.5 |
| Nominal Diameter (Metric) | 63.5 |
| Wall Thickness WT (Imperial) | 0.025 |
| Wall Thickness WT (Metric) | 0.64 |
| Material | Aluminum (AL) Glass Fiber (GF) |
| Material Shortcut | AL GF |
| Halogen Free | Yes |

| | |
|------------------------------|-----------------------------------|
| UV Resistant (Yes/No) | No |
| Use Conditions | For Indoor Use Only |
| Operating Temperature | -76°F to +491°F (-60°C to +255°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 50 |
| Package Quantity (Metric) | 15.24 |
| Customs Number | 7019905150 |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)