

## Specification Sheet

Part Number: 170-03193



A layer of aluminum provides protection from chemicals, scraping, cuts and abrasion.

Additional layer also provides insulation barrier for vulnerable wires and cables within high temperature environments.

Cuts with ordinary scissors for fast, easy application.

Braided Wrap, Aluminum Laminated Fiberglass, 4' Long Stick, 5/8" Dia, AL/GF, Silver, 20/box

Article Number 170-03193

Type BSHTTSW58SB

Color Silver (SR)

Quantity Per pack

Product Description Aluminum Laminated Fiberglass Wrap sleeving combines the protection of bonded aluminum and fiberglass into a robust solution that deflects radiant heat away from sensitive wires and cables. Wrap-around design allows for fast and easy installation and maintenance. Sold in 4-foot sticks.

Short Description Braided Wrap, Aluminum Laminated Fiberglass, 4' Long Stick, 5/8" Dia, AL/GF, Silver, 20/box

Global Part Name	BSHTTSW58SB-GF-AL-SR
Length L (Imperial)	4.0
Length L (Metric)	1.22
Bundle Diameter Min (Imperial)	0.1
Bundle Diameter Min (Metric)	2.54
Bundle Diameter Max (Imperial)	0.5
Bundle Diameter Max (Metric)	12.7
Diameter D (Imperial)	0.63
Diameter D (Metric)	16.0
Nominal Diameter (Imperial)	0.63
Nominal Diameter (Metric)	16.00
Wall Thickness WT (Imperial)	0.042
Wall Thickness WT (Metric)	1.06
Material	Glass fiber with aluminium foil (GF-AL)
Material Shortcut	GF-AL

Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-76°F to +491°F (-60°C to +255°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	20
Package Quantity (Metric)	20
Customs Number	7019905150

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)