

Specification Sheet

Part Number: 170-03203



Tightly woven fabric bundles and protects cables and hoses from sunlight and abrasion damage; also deflects high pressure hose ruptures.

Nylon material resists gasoline, salt and other chemicals.

Cut to size easily with regular scissors.

Braided Sleeving, Heavy Duty, 1" Dia, PA6, Black, 50 ft/reel

Article Number 170-03203

Type BSHDWV

Color Black (BK)

Quantity Per pack

Product Description Sleeving made of a tightly woven nylon fabric, slides onto hoses, cables and components to protect them from abrasion and environmental elements, including UV damage. Also protects surrounding surfaces from damage.

Short Description Braided Sleeving, Heavy Duty, 1" Dia, PA6, Black, 50 ft/reel

Global Part Name BSHDWV-PA6-BK

| | |
|--------------------------------|-------------------|
| Length L (Imperial) | 50.0 |
| Length L (Metric) | 15.24 |
| Bundle Diameter Min (Imperial) | 0.1 |
| Bundle Diameter Min (Metric) | 2.54 |
| Bundle Diameter Max (Imperial) | 0.95 |
| Bundle Diameter Max (Metric) | 24.1 |
| Diameter D (Imperial) | 1.0 |
| Diameter D (Metric) | 25.4 |
| Nominal Diameter (Imperial) | 1 |
| Nominal Diameter (Metric) | 25.4 |
| Wall Thickness WT (Imperial) | .045 |
| Wall Thickness WT (Metric) | 1.14 |
| Material | Polyamide 6 (PA6) |
| Material Shortcut | PA6 |
| Halogen Free | Yes |

| | |
|------------------------------|-----------------------------------|
| UV Resistant (Yes/No) | No |
| Use Conditions | For Indoor and Outdoor Use |
| Operating Temperature | -49°F to +248°F (-45°C to +120°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 50 |
| Package Quantity (Metric) | 15.24 |
| Customs Number | 5806322000 |

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)