

## Specification Sheet

Part Number: 181-00219

Strong fingers prevent unintended breaking.

Fingers are easily deflected outward, allowing easier positioning of the wires.

Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.

Nonpermanent adhesive allows repositioning prior to final installation.

Optional covers snap on and off easily, and their nonslip lining ensures they stay in place even under vibration.



Slotted Wall Wiring Duct, 2.5" x 3", Adhesive, PVC, White, 30ft/Box

Article Number 181-00219

Type SLA2.5X3

Color White (WH)

Quantity Per pack

Product Description HellermannTyton Slotted Wall Duct features breakaway fingers that provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a wider opening is required. The lower score line allows the sidewall to be smoothly cut for joints and Ts. Pressure-sensitive, rubber-based adhesive backing aids in temporary positioning.

|                                  |   |
|----------------------------------|---|
| Short Description                | Slotted Wall Wiring Duct, 2.5" x 3", Adhesive, PVC, White, 30ft/Box |
| Global Part Name                 | SLA2.5X3-PVC-WH   |
| Length L (Imperial)              | 6.0   |
| Length L (Metric)                | 1.83  |
| Width W (Imperial)               | 2.5   |
| Width W (Metric)                 | 63.5  |
| Height H (Imperial)              | 3.07  |
| Height H (Metric)                | 77.9  |
| Mounting Hole Centers (Imperial) | 4.0   |
| Material                         | Polyvinylchloride (PVC)   |
| Material Shortcut                | PVC   |
| Flammability                     | UL 94 V-0   |
| Halogen Free                     | No  |
| UV Resistant (Yes/No)            | No  |
| Use Conditions                   | For Indoor Use Only   |

|                              |  |
|------------------------------|--|
| Operating Temperature        | +122°F (+50°C)                                   |
| Reach Compliant (Article 33) | No   |
| ROHS Compliant               | Yes  |
| Certification/Specification  | CSA EN 50085-2-3_1A EN 50085-1:2005 + A1:2013 UL |
| UL Recognized (US)           | Yes  |
| Package Quantity (Imperial)  | 30.0   |
| Package Quantity (Metric)    | 9.14   |
| Customs Number               | 3925900000                                       |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)