

Specification Sheet

Part Number: 181-00306



Dividers have continuous score lines for smooth breakouts.

Top of the dividers has a double-sided lip which reduces the likelihood of wires falling out during installation.

Article Number	181-00306
Type	DV1.5
Color	White (WH)
Quantity Per	carton
Product Description	Solid-Wall Dividers can be securely mounted into all types of HellermannTyton wiring duct to separate high and low voltage, thus reducing interference. The dividers simply snap or slide into the specially designed mount, instantly creating multiple channels within a single duct size.
Short Description	Wiring Duct Divider, 1.5" High, PVC, White, 120 ft/carton
Global Part Name	DV1.5-PVC-WH

Length L (Imperial)	6.0
Length L (Metric)	1.83
Width W (Imperial)	0.75
Width W (Metric)	19.05
Thickness T (Imperial)	0.06
Thickness T (Metric)	1.52
Height H (Imperial)	1.40
Height H (Metric)	35.6
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	+122°F (+50°C)
Reach Compliant (Article 33)	No

ROHS Compliant	Yes
Certification/Specification	UL EN 50085-1:2005 + A1:2013 EN 50085-2-3_1A
UL Recognized (US)	Yes
Package Quantity (Imperial)	120.0
Package Quantity (Metric)	36.58
Customs Number	3925900000

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)