

Specification Sheet

Part Number: 181-15404



- Strong fingers prevent unwanted breaking.
- Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.
- Supplied with mounting holes to streamline installation.
- Optional covers enhance protection and appearance.

Slotted Wall Wiring Duct, 1.5" x 4", Non-Adhesive, PVC, Gray, 60ft/Carton

Article Number	181-15404
Type	SL1.5X4
Color	Gray (GY)
Quantity Per	carton
Product Description	HellermannTyton Slotted Wall Wiring Duct features break-away fingers that provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and T's.
Short Description	Slotted Wall Wiring Duct, 1.5" x 4", Non-Adhesive, PVC, Gray, 60ft/Carton

Global Part Name SL1.5X4-PVC-GY

Length L (Imperial) 6.0

Length L (Metric) 1.83

Fixation Method Non-Adhesive

Width W (Imperial) 1.5

Width W (Metric) 38.1

Height H (Imperial) 4.07

Height H (Metric) 103.4

Mounting Hole Centers (Imperial) 4.0

Material Polyvinylchloride - rigid extrusion grade (PVC)

Material Shortcut PVC

Flammability UL 94 V-0

Halogen Free No

UV Resistant (Yes/No) No

Use Conditions For Indoor Use Only

Operating Temperature	+122°F (+50°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	CSA EN 50085-2-3_1A EN 50085-1:2005 + A1:2013 UL
UL Recognized (US)	Yes
Package Quantity (Imperial)	60
Package Quantity (Metric)	18.3
Customs Number	3925900000

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)