

Specification Sheet

Part Number: 181-92015



A temporary film is applied to the covers to protect against scratches and is writable for identification during installation.

Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement.

Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off. (Covers to be purchased separately)

Wiring Duct Cover for 2" Duct, 6 ft Long, PVC, Black, 30ft/box

Article Number	181-92015
Type	TC2
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton’s Pro-Duct wiring duct covers are sold separately and interchangeable among the 3 styles of duct (solid, slotted and high density). Manufactured from high impact, rigid PVC, Pro-Duct covers come in standard colors of white, gray and black. Wiring duct covers are available in 6 foot lengths.
Short Description	Wiring Duct Cover for 2" Duct, 6 ft Long, PVC, Black, 30ft/box

Global Part Name	TC2-PVC-BK
Length L (Imperial)	6.0
Length L (Metric)	1.83
Width W (Imperial)	2.0
Width W (Metric)	50.8
Height H (Imperial)	0.308
Height H (Metric)	7.82
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+122°F (+50°C)
Reach Compliant (Article 33)	No

ROHS Compliant	Yes
Certification/Specification	CSA EN 50085-1:2005 + A1:2013 UL EN 50085-2-3_1A
UL Recognized (US)	Yes
Package Quantity (Imperial)	30.0
Package Quantity (Metric)	9.14
Customs Number	3925900000

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com