

Specification Sheet

Part Number: 183-21080

Excellent fire-safety characteristics.

Narrow slots suitable for small-diameter wires.

Smooth, burr-free edges protect installers from injury and wires from damage.

Fingers can be removed with no sharp edges at pre-notched snap-off points.

Further pre-notched snap-off point at base of sidewall allow cutting out and removing sections of sidewall with no sharp edges.

Duct covers hold securely even in a vertical position and under vibration.

Cover is flush with side of duct, allowing for tight, contiguous placement of duct.

Base perforation according to DIN EN 50085.



Halogen Free Slotted Wiring Duct & Cover, without Adhesive, 100mm x 80mm, Piece/ABS, Gray, 12 m/Box

Article Number 183-21080

Type HTWD-HF-100X80

Color Gray (GY)

Quantity Per pack

Product Description	HelaDuct HTWD-HF wiring duct is used to route and protect wires in control panels and switching systems where there are high demands on personal or material safety in case of fire, such as in public transport, tunnels, data processing centers or public buildings.
Short Description	Halogen Free Slotted Wiring Duct & Cover, without Adhesive, 100mm x 80mm, Piece/ABS, Gray, 12 m/Box
Global Part Name	HTWD-HF-100X80-PC/ABS-GY
Length L (Imperial)	6.56
Length L (Metric)	2.0
Fixation Method	Screw Mounting
Width W (Imperial)	3.94
Width W (Metric)	100.0
Height H (Imperial)	3.15
Height H (Metric)	80.0
Material	Acrylonitrile Butadiene Styrene alloyed with Polycarbonate (PC/ABS)
Material Shortcut	PC/ABS
Flammability	UL 94 V-0

Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-13°F to +194°F (-25°C to +90°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 62275 UL ANSI/UL 1565 EN [45545-2] UL CSA -C22.2 no. 62275 UL CSA -C22.2 no. 18.5
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	12
Package Quantity (Metric)	12.0
Customs Number	3925900000

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)