

Specification Sheet

Part Number: D20L4



Available in three sizes, HellermannTyton screw mount clips offer quick, snap-in action.

These clips allow for easy release for wiring changes or replacements, saving both time and money.

Screw Mount Cable Clip, 0.79" Max Bundle Dia, 0.31" Mounting Hole Dia, POM, Black, 200/pkg

Article Number	211-70204
Type	8D20
Color	Black (BK)
Quantity Per	pack
Product Description	Developed for fixing pipes, cables and hoses, the D-Clips elastic locking system ensures optimal fixing and at the same time, easy removal of the fixed elements by simply pressing the lower latch down and pulling the fixed element.
Short Description	Screw Mount Cable Clip, 0.79" Max Bundle Dia, 0.31" Mounting Hole Dia, POM, Black, 200/pkg
Global Part Name	8D20-POM-BK

Length L (Imperial)	1.10
Length L (Metric)	28.0
Fixation Method	screw-hole
Variant	Closed
Width W (Imperial)	0.59
Width W (Metric)	15.0
Bundle Diameter Min (Imperial)	0.79
Bundle Diameter Min (Metric)	20.0
Bundle Diameter Max (Imperial)	0.79
Bundle Diameter Max (Metric)	20.0
Nominal Diameter (Imperial)	0.75
Nominal Diameter (Metric)	20.0
Wall Thickness WT (Imperial)	0.10
Wall Thickness WT (Metric)	2.5
Mounting Hole Diameter D (Imperial)	0.31
Mounting Hole Diameter D (Metric)	8.0 mm

Mounting Hole Diameter D Max (Metric) 8.0

Material Polyacetal (POM)

Material Shortcut POM

Flammability UL 94 HB

UV Resistant (Yes/No) No

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +194°F (-40°C to +90°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 200

Package Quantity (Metric) 200

Customs Number 3926909988

