

Specification Sheet

Part Number: 211-60061



P-Clamps easily guide and locate wire and cables up to 1" in diameter.

Designed with a radius edge to prevent chafing and cutting into insulation.

P-Clamp, 0.39" Wide, 0.43" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66HS Black, 1000/pkg

Article Number	211-60061
----------------	-----------

Type	H6P
------	-----

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton P-Clamps easily guide and locate wires and cables. The clamps are designed with a radius edges to prevent chafing and cutting into insulation. Available sizes up to 1" bundle diameters.
---------------------	---

Short Description	P-Clamp, 0.39" Wide, 0.43" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66HS Black, 1000/pkg
-------------------	--

Global Part Name	H6P-PA66HS-BK
------------------	---------------

Fixation Method	screw-hole
Variant	Closed
Width W (Imperial)	0.39
Width W (Metric)	10.0
Bundle Diameter Max (Imperial)	0.43
Bundle Diameter Max (Metric)	11.0
Nominal Diameter (Imperial)	0.44
Nominal Diameter (Metric)	11.0
Wall Thickness WT (Imperial)	0.047
Wall Thickness WT (Metric)	1.2
Mounting Hole Diameter D (Imperial)	0.17 "
Mounting Hole Diameter D (Metric)	4.2 mm
Mounting Hole Diameter D Max (Metric)	4.2
Mounting Hole Centers (Imperial)	0.51
Material	Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)