

Specification Sheet

Part Number: 309-20483

Quick and easy shrinking TF21 tubing is widely used for insulating, mechanical protection, strain relief, marking, and bundling.

The excellent balance of electrical, mechanical and chemical properties meet and exceed industrial standards.

TF21 is UL-224 listed and available in a wide range of sizes and colors.



Heat Shrink Tubing, Bulk Reel, 2:1 Shrink Ratio, 3/16", 4.8/2.4 Dia, PO, Orange, 246.0 ft/reel

Article Number	309-20483
----------------	-----------

Type	TF21-4.8/2.4
------	--------------

Color	Orange (OG), High Voltage (HV)
-------	--------------------------------

Quantity Per	pack
--------------	------

Product Description	TF21 is a highly flexible thin wall heat shrink tubing with a 2-to-1 shrink ratio and excellent flame retardant properties. In addition to providing insulation and abrasion protection for wires and cables, the polyolefin material also offers resistance to oils, solvents and chemicals. TF21 is UL Recognized with a UL 224 VW-1 flame rating.
---------------------	--

Short Description	Heat Shrink Tubing, Bulk Reel, 2:1 Shrink Ratio, 3/16", 4.8/2.4 Dia, PO, Orange, 246.0 ft/reel
-------------------	--

Global Part Name	TF21-4.8/2.4-PO-X-OG
Variant	Thin-Wall
Bundle Diameter Min (Imperial)	0.094
Bundle Diameter Min (Metric)	2.4
Bundle Diameter Max (Imperial)	0.18
Bundle Diameter Max (Metric)	4.8
Wall Thickness WT (Imperial)	0.02
Wall Thickness WT (Metric)	0.51
Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
Flammability	ASTM D876
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-67°F to +275°F (-55°C to +135°C)

Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 224
UL Recognized (US)	Yes
Package Quantity (Imperial)	246
Package Quantity (Metric)	75
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com