

Specification Sheet

Part Number: 309-65302


Thin, 2 to 1 shrink ratio tubing provides insulation and abrasion protection for wires and cables.

Flammability rating of UL224 VW-1 for use in applications requiring the highest degree of flame protection (excludes clear tubing).

Flexible-yet-durable material resists most common oils, chemicals and fluids.

Available in a variety of diameters and colors for identifying and marking wires and cables.

Available in mini reels, bulk reels, and sticks for small to large volume applications.



Heat Shrink Tubing, 4' Long Stick, 2:1 Shrink Ratio, 1.50", 38.1/19.1 Dia, PO, Red, 6/pkg

Article Number	309-65302
Type	TFN21-ST 38.1/19.1
Color	Red (RD)
Quantity Per	pack

Product Description	TFN21 is a highly flexible thin wall heat shrink tubing with a 2 to 1 shrink ratio and excellent flame retardant properties. In addition to providing insulation and abrasion protection for wires and cables, the polyolefin material also offers resistance to oils, solvents and chemicals. Available in mini reels, bulk reels and sticks, for small to large volume applications.
Short Description	Heat Shrink Tubing, 4' Long Stick, 2:1 Shrink Ratio, 1.50", 38.1/19.1 Dia, PO, Red, 6/pkg
Global Part Name	TFN21-ST 38.1/19.1-PO-X-RD
Variant	Thin-Wall
Nominal Diameter (Imperial)	1.5
Nominal Diameter (Metric)	38.1
Wall Thickness WT (Imperial)	.039
Wall Thickness WT (Metric)	1.00
Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
Flammability	UL 224 VW-1
Halogen Free	No
UV Resistant (Yes/No)	No

Use Conditions	For Indoor Use Only
Operating Temperature	-67°F to +275°F (-55°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 224 CSA
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	6
Package Quantity (Metric)	6
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com