

Specification Sheet

Part Number: 553-50005

Slide Slit and optional center slits for easy wire insertion.

Smooth surface for clean and legible printing.

Supplied on a ladder style carrier so that markers can be kitted after printing.

A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.



ShrinkTrak Labels, 1-Sided, Unslit, 0.125" (3.17mm), PO-X, Yellow, 250/box

Article Number	553-50005
----------------	-----------

Type	HST3-1YE
------	----------

Color	Yellow (YE)
-------	-------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.
---------------------	---

Short Description	ShrinkTrak Labels, 1-Sided, Unslit, 0.125" (3.17mm), PO-X, Yellow, 250/box
-------------------	--

Global Part Name	HST3-1YE-PO-X-YE
------------------	------------------

Variant	Thin-Wall
---------	-----------

Width W (Imperial)	1.9
--------------------	-----

Width W (Metric)	48.26
------------------	-------

Thickness T (Imperial)	.003
------------------------	------

Thickness T (Metric)	.0762
----------------------	-------

Height H (Imperial)	0.235
---------------------	-------

Height H (Metric)	5.69
-------------------	------

Width of Liner (Metric)	76.2
-------------------------	------

Width of Liner (Imperial)	3.0
---------------------------	-----

Outside Diameter OD (Imperial)	0.125
--------------------------------	-------

Outside Diameter OD (Metric)	3.2
------------------------------	-----

Outside Diameter Max (Imperial)	0.125
---------------------------------	-------

Outside Diameter Max (Metric)	3.2
-------------------------------	-----

Wall Thickness WT (Imperial)	0.031
------------------------------	-------

Wall Thickness WT (Metric)	0.79
----------------------------	------

Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	SAE-AS81531 SAE-AMS-DTL-23053/5 Class 1 and 3 MIL-STD-202G Method 215K
Flammability	UL 224 VW-1
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-67°F to +275°F (-55°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 224 125 °C 600V VW-1
Package Quantity (Imperial)	250
Package Quantity (Metric)	250
Customs Number	3917320000

Labels per Column1

Labels per Row1

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)