

Specification Sheet


Part Number: 553-50017

Slide Slit and optional center slits for easy wire insertion.

Smooth surface for clean and legible printing.

Supplied on a ladder style carrier so that markers can be kitted after printing.

A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.



ShrinkTrak Labels, 1-Sided, Unslit, 0.25" (6.35mm), PO-X, White, 1000/box

Article Number	553-50017
----------------	-----------

Type	HST6-2WH
------	----------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.
---------------------	---

Short Description	ShrinkTrak Labels, 1-Sided, Unslit, 0.25" (6.35mm), PO-X, White, 1000/box
-------------------	---

Global Part Name	HST6-2WH-PO-X-WH
------------------	------------------

Variant	Thin-Wall
---------	-----------

Width W (Imperial)	1.9
--------------------	-----

Width W (Metric)	48.26
------------------	-------

Thickness T (Imperial)	.003
------------------------	------

Thickness T (Metric)	.0762
----------------------	-------

Height H (Imperial)	0.42
---------------------	------

Height H (Metric)	10.67
-------------------	-------

Width of Liner (Metric)	76.2
-------------------------	------

Width of Liner (Imperial)	3.0
---------------------------	-----

Outside Diameter OD (Imperial)	0.25
--------------------------------	------

Outside Diameter OD (Metric)	6.35
------------------------------	------

Outside Diameter Max (Imperial)	0.25
---------------------------------	------

Outside Diameter Max (Metric)	6.35
-------------------------------	------

Wall Thickness WT (Imperial)	0.028
------------------------------	-------

Wall Thickness WT (Metric)	0.71
----------------------------	------

Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	SAE-AS81531 SAE-AMS-DTL-23053/5 Class 1 and 3 MIL-STD-202G Method 215K
Flammability	UL 224 VW-1
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-67°F to +275°F (-55°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	SAE - AS81531 SAE - AMS - DTL-23053/5 Class 1 and 3 UL 224 125 °C 600V VW-1
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3917320000

Labels per Column 1

Labels per Row 1

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)