

## Specification Sheet

Part Number: 553-50027

Slide Slit and optional center slits for easy wire insertion.

Smooth surface for clean and legible printing.

Supplied on a ladder style carrier so that markers can be kitted after printing.

A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.



ShrinkTrak Labels, 1-Sided, 1-Slit, 0.38" (9.52mm), PO-X, Yellow, 500/box

|                |           |
|----------------|-----------|
| Article Number | 553-50027 |
|----------------|-----------|

|      |            |
|------|------------|
| Type | HST9-3YE-S |
|------|------------|

|       |             |
|-------|-------------|
| Color | Yellow (YE) |
|-------|-------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                                                                                                                                                                       |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production. |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                   |                                                                           |
|-------------------|---------------------------------------------------------------------------|
| Short Description | ShrinkTrak Labels, 1-Sided, 1-Slit, 0.38" (9.52mm), PO-X, Yellow, 500/box |
|-------------------|---------------------------------------------------------------------------|

|                  |                    |
|------------------|--------------------|
| Global Part Name | HST9-3YE-S-PO-X-YE |
|------------------|--------------------|

|         |           |
|---------|-----------|
| Variant | Thin-Wall |
|---------|-----------|

|                    |      |
|--------------------|------|
| Width W (Imperial) | 0.95 |
|--------------------|------|

|                  |       |
|------------------|-------|
| Width W (Metric) | 24.13 |
|------------------|-------|

|                        |      |
|------------------------|------|
| Thickness T (Imperial) | .003 |
|------------------------|------|

|                      |       |
|----------------------|-------|
| Thickness T (Metric) | .0762 |
|----------------------|-------|

|                     |       |
|---------------------|-------|
| Height H (Imperial) | 0.597 |
|---------------------|-------|

|                   |       |
|-------------------|-------|
| Height H (Metric) | 15.16 |
|-------------------|-------|

|                         |      |
|-------------------------|------|
| Width of Liner (Metric) | 76.2 |
|-------------------------|------|

|                           |     |
|---------------------------|-----|
| Width of Liner (Imperial) | 3.0 |
|---------------------------|-----|

|                                |       |
|--------------------------------|-------|
| Outside Diameter OD (Imperial) | 0.375 |
|--------------------------------|-------|

|                              |      |
|------------------------------|------|
| Outside Diameter OD (Metric) | 9.52 |
|------------------------------|------|

|                                 |       |
|---------------------------------|-------|
| Outside Diameter Max (Imperial) | 0.375 |
|---------------------------------|-------|

|                               |      |
|-------------------------------|------|
| Outside Diameter Max (Metric) | 9.52 |
|-------------------------------|------|

|                              |       |
|------------------------------|-------|
| Wall Thickness WT (Imperial) | 0.031 |
|------------------------------|-------|

|                            |      |
|----------------------------|------|
| Wall Thickness WT (Metric) | 0.79 |
|----------------------------|------|

|                              |                                                                              |
|------------------------------|------------------------------------------------------------------------------|
| Material                     | Polyolefin, cross-linked (PO-X)                                              |
| Material Shortcut            | PO-X                                                                         |
| US MIL SPEC                  | MIL-STD-202G Method 215K<br>SAE-AS81531<br>SAE-AMS-DTL-23053/5 Class 1 and 3 |
| Flammability                 | UL 224 VW-1                                                                  |
| Halogen Free                 | No                                                                           |
| UV Resistant (Yes/No)        | No                                                                           |
| Use Conditions               | For Indoor Use Only                                                          |
| Operating Temperature        | -67°F to +275°F (-55°C to +135°C)                                            |
| Reach Compliant (Article 33) | Yes                                                                          |
| ROHS Compliant               | Yes                                                                          |
| Certification/Specification  | UL 224 125 °C 600V VW-1 SAE - AS81531 SAE - AMS - DTL-23053/5 Class 1 and 3  |
| Package Quantity (Imperial)  | 500                                                                          |
| Package Quantity (Metric)    | 500                                                                          |
| Customs Number               | 3917320000                                                                   |

Labels per Column 1

Labels per Row 2

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)