

Specification Sheet

Part Number: 553-50068

Slide Slit and optional center slits for easy wire insertion.

Smooth surface for clean and legible printing.

Supplied on a ladder style carrier so that markers can be kitted after printing.

A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.



ShrinkTrak Labels, 1-Sided, 2-Slit, 0.187" (4.74mm), PO-X, White, 750/box

Article Number

553-50068

Type

HST4.8-1.6WH-2S

Color

White (WH)

Quantity Per

pack

Product Description

HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.

Short Description

ShrinkTrak Labels, 1-Sided, 2-Slit, 0.187" (4.74mm), PO-X, White, 750/box

Global Part Name	HST4.8-1.6WH-2S-PO-X-WH
------------------	-------------------------

Variant	Thin-Wall
---------	-----------

Width W (Imperial)	0.63
--------------------	------

Width W (Metric)	16.0
------------------	------

Thickness T (Imperial)	.003
------------------------	------

Thickness T (Metric)	.0762
----------------------	-------

Height H (Imperial)	0.312
---------------------	-------

Height H (Metric)	7.92
-------------------	------

Width of Liner (Metric)	76.2
-------------------------	------

Width of Liner (Imperial)	3.0
---------------------------	-----

Outside Diameter OD (Imperial)	0.187
--------------------------------	-------

Outside Diameter OD (Metric)	4.74
------------------------------	------

Outside Diameter Max (Imperial)	0.187
---------------------------------	-------

Outside Diameter Max (Metric)	4.74
-------------------------------	------

Wall Thickness WT (Imperial)	0.026
------------------------------	-------

Wall Thickness WT (Metric)	0.66
----------------------------	------

Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	SAE-AMS-DTL-23053/5 Class 1 and 3 MIL-STD-202G Method 215K SAE-AS81531
Flammability	UL 224 VW-1
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-67°F to +275°F (-55°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	CEN
Package Quantity (Imperial)	750
Package Quantity (Metric)	750
Customs Number	3917320000

Labels per Column 1

Labels per Row 3

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)