

Specification Sheet

Part Number: 553-60052

Halogen free, for low smoke propagation, density and toxicity.

50 mm, 25 mm and 16 mm pre-cut marker options as standard, for ability to get multiple labels out of one tag.

Product Image

Delivery in convenient storage boxes for protection.

ShrinkTrak Labels, 2-Sided, 2-Slit, Halogen Free, 0.63" x 1.69", Polyolefin, White, 3000/pkg

Article Number

553-60052

Type

TLFX254DS-3x16WH

Color

White (WH)

Quantity Per

pack

Product Description

ShrinkTrak DS is a halogen-free, double-sided heat shrinkable marker with a 2:1 shrink ratio. HellermannTyton's unique ladder-style design assists in removing markers off the carrier. The side slits have been designed to ensure the wire entry gap is as large as possible while remaining on the carrier strip, enabling the user to quickly insert wire and cable into the marker. For a complete labeling solution, ShrinkTrak DS can be printed using HellermannTyton's TagPrint® Pro professional label creation software and thermal transfer printers. For double-sided printing, HellermannTyton's TrakMark DS double-sided printer produces excellent results. Choose among multiple ribbon types to create a permanent print that resists most solvents when shrunk and applied.

Short Description

ShrinkTrak Labels, 2-Sided, 2-Slit, Halogen Free, 0.63" x 1.69", Polyolefin, White, 3000/pkg

Global Part Name

TLFX254DS-3x16WH-PO-X-WH

Fixation Method	Suspend
Variant	Roller form
Width W (Imperial)	0.63
Width W (Metric)	16.0
Thickness T (Imperial)	.0130
Thickness T (Metric)	.29
Height H (Imperial)	1.69
Height H (Metric)	43.0
Width of Liner (Metric)	88.9
Width of Liner (Imperial)	3.50
Outside Diameter Max (Imperial)	1.0
Outside Diameter Max (Metric)	25.4
Wall Thickness WT (Imperial)	0.036
Wall Thickness WT (Metric)	0.925
Material	Polyolefin, cross-linked (PO-X)

Material Shortcut	PO-X
US MIL SPEC	SAE AS5942 3.4.1 MIL-STD-202J
Flammability	UL 224
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-67°F to +221°F (-55°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	ASTM E 662 ASTM E 162 ASTM 1354 EN [45545-2] NFPA 130 compliant
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3917320000

