

Specification Sheet

Part Number: TT822OUT10SM



- Ribbons are resin based for the best print durability.
- Ribbons are available to fit all HellermannTyton printers for easy resupply.
- Ribbons are available in colors for maximizing design printing capabilities.
- Ribbons meet UL recognition and Military standard where applicable to meet specific industry label requirements.

Thermal Transfer Ribbon, 4.33" x 299', 0.5" Core, 822 Resin, Black, 1/pkg

Article Number	556-00146
Type	TT822OUT10SM
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton thermal transfer ribbons are designed for use in HellermannTyton thermal transfer printers. Available on 1/2" and 1" cores, the ribbons are coated side out and available in two different lengths. All ribbons are available in a variety of colors and are matched to the HellermannTyton label stock to give the best chemical and abrasion resistance.
Short Description	Thermal Transfer Ribbon, 4.33" x 299', 0.5" Core, 822 Resin, Black, 1/pkg

Global Part Name	TT822OUT10SM-PET-BK
Length L (Imperial)	229.0
Length L (Metric)	74
Variant	Colored ribbon
Width W (Imperial)	4.33
Width W (Metric)	110.0
Material	Polyester Film (PET)
Material Shortcut	PET
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	+40°F to +300°F (+4°C to +82°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1

Package Quantity (Metric)	1
Customs Number	3702440160

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)