

Specification Sheet

Part Number: TTHSTOUT

Clean Start ribbons prolong printhead life, while reducing maintenance costs.

Ribbons are resin based for the best print durability.

Ribbons are available to fit all HellermannTyton printers for easy resupply.

Ribbons meet UL recognition and Military standard where applicable to meet specific industry label requirements.



Clean Start Thermal Transfer Ribbon, 4.0" x 984', 1.0" Core, PET, Black, 1/pkg

Article Number	556-00162
----------------	-----------

Type	TTHSTOUT
------	----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton Clean Start thermal transfer ribbons incorporate an innovative, patented printhead cleaner built right into the ribbon. Clean Start ribbon removes debris before it builds up on the printhead, extending printer life. Available on 1/2" and 1" cores, the ribbons are coated side out and available in two different lengths. All ribbons are available in a variety of colors and are matched to the HellermannTyton label stock to give the best chemical and abrasion resistance.
---------------------	---

Short Description	Clean Start Thermal Transfer Ribbon, 4.0" x 984', 1.0" Core, PET, Black, 1/pkg
Global Part Name	TTHSTOUT-PET-BK
Local Order Number 2	shipping dimension 2.5" X 4.0"
Length L (Imperial)	984.0
Length L (Metric)	300
Variant	Colored ribbon
Width W (Imperial)	4.0
Width W (Metric)	101.6
Material	Polyester Film (PET)
Material Shortcut	PET
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	+40°F to +300°F (+4°C to +82°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	3702390100

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)