

## Specification Sheet

Part Number: 556-00240

300 dpi print head for high resolution printing.

Label holder included for easy loading of any size media.

Lightweight with a small footprint for easy transport to jobs sites or around the shop.

LCD user interface for easier setup, diagnostics and adjustments.

Ethernet ready for easy network connectivity.

Print speeds up to 3 in (76.2mm) per second for fast label production.

2mb flash/8mb DRAM for accepting large label files that require a lot of data.

Highly accurate sensor means there is no need to calibrate during label changes and eliminates most common printer errors.



TT230SMC Thermal Transfer Printer with Cutter, 300 dpi, Black, 1/pkg

Article Number 556-00240

Type TT230SMC

Color Black (BK)

Quantity Per pack

**Product Description**

HellermannTyton's TT230 Series thermal transfer printers are designed for low- to medium-volume printing of thermal transfer labels and ShrinkTrak. They deliver optimal performance not found in other small desktop printers. This lightweight printer offers high speed, precision and flexible printing with the ability to print on most HellermannTyton labels and ShrinkTrak. Used in conjunction with TagPrint Pro, the printers offer error-free printing and seamless operation. TT230SM is the standard printer; TT230SMC includes a cutter. TT230SMCKB includes a cutter and a USB keyboard as well as a built-in database of the required NEC2014 and NEC2017 labels. Simply select the image of the label you wish to print in the LCD screen and print any quantity. Users can also enter and print needed calculations on code-compliant, pre-saved label designs. No additional software needed.

**Short Description**

TT230SMC Thermal Transfer Printer with Cutter, 300 dpi, Black, 1/pkg

**Global Part Name**

TT230SMC-PL-BK

**Length L (Imperial)**

11.75

**Length L (Metric)**

298.5

**Width W (Imperial)**

7.95

**Width W (Metric)**

202

**Height H (Imperial)**

6.81

**Height H (Metric)**

173

**Material**

Plastic (PL)

**Material Shortcut**

PL

UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+40°F to +104°F (+4°C to +40°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8443321050

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)