

Specification Sheet

Part Number: 556-00256

300 dpi print head for high resolution printing.

Label holder included for easy loading of any size media.

Lightweight with a small footprint for easy transport to jobs sites or around the shop.

LCD user interface for easier setup, diagnostics and adjustments.

Ethernet ready for easy network connectivity.

Print speeds up to 3 in (76.2mm) per second for fast label production.

2mb flash/8mb DRAM for accepting large label files that require a lot of data.

Highly accurate sensor means there is no need to calibrate during label changes and eliminates most common printer errors.



TT230SMC Printer Kit with Cutter, 1/pkg

Article Number 556-00256

Type TT230SMC KIT

Color Black (BK)

Quantity Per pack

Product Description

HellermannTyton's TT230 Series thermal transfer printers are designed for low- to medium-volume printing of thermal transfer labels and ShrinkTrak. They deliver optimal performance not found in other small desktop printers. This lightweight printer offers high speed, precision and flexible printing with the ability to print on most HellermannTyton labels and ShrinkTrak. Used in conjunction with TagPrint Pro, the printers offer error-free printing and seamless operation. Each kit contains one TT230SMC printer (556-00240), a carrying case (556-00231), one black and one white ribbon (TT822OUTSM) and (556-00190), label holder (556-00235) and TagPrint Pro 4.0 software (556-00035).

Short Description

TT230SMC Printer Kit with Cutter, 1/pkg

Global Part Name

TT230SMC KIT-PL-BK

Contents of pkg/kit

One TT230SMC printer with cutter, label caddy, TagPrint® Pro label design software, black ribbon, white ribbon, and a high-quality hard-shell carrying case.

Length L (Imperial)

11.75

Length L (Metric)

298.5

Width W (Imperial)

7.95

Width W (Metric)

202

Height H (Imperial)

13.5

Height H (Metric)

342.9

Material

Plastic (PL)

Material Shortcut	PL
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+40°F to +104°F (+4°C to +40°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8443321050

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)