

Specification Sheet

Part Number: 556-00443



300 dpi print head for high resolution printing.

Ethernet ready for easy network connectivity.

Floating print head to automatically adjust to varying media thickness such as printable heat shrink tubing.

Optional cutter faceplate for automatic cutting and kitting of printed labels.

Article Number

556-00443

Type

TTM430-SC

Color

Various (MIX)

Quantity Per

pack

Product Description

HellermannTyton's TTM430/TTM460 thermal transfer printers are designed for medium to high volume users of thermal transfer labels and ShrinkTrak. The user-friendly design features a streamlined menu for simple navigation, while the built in caddy allows even the largest label rolls to fit inside the printer. The optional cutter can cut through the thickest material. The TTM430/TTM460 printers are designed to handle all sizes of HellermannTyton's ShrinkTrak markers, and the TTM430/TTM460 can print on even the smallest labels.

Short Description

TTM430SC Thermal Transfer Printer, 300 dpi, Gray, 1/Pkg

Global Part Name	TTM430-SC-DIV-MIX
Length L (Imperial)	16.0
Length L (Metric)	406.4
Width W (Imperial)	9.4
Width W (Metric)	240
Height H (Imperial)	12.28
Height H (Metric)	312
Material	Various (DIV)
Material Shortcut	DIV
UV Resistant (Yes/No)	No
Operating Temperature	+40°F to +104°F (+4°C to +40°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes

Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8443321050

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)