

Specification Sheet

Part Number: 558-00310

Pre-printed header striped continuous vinyl rolls come in different header colors, providing a variety of printing options.

The headers can be printed with various ARC FLASH, WARNING And CAUTION headlines to meet OSHA safety standards for identifying electrical panels and equipment.



Signs can be designed in TagPrint Pro labeling software and printed with any HellermannTyton thermal transfer printing system with optional cutter attached.

Thermal Transfer Adhesive Labels, Solid Color Continuous Roll, 1.0 x 250', UV Stable VL, Yellow, 250 ft/roll

Article Number	558-00310
----------------	-----------

Type	HT1YE250
------	----------

Color	Yellow (YE)
-------	-------------

Quantity Per	pack
--------------	------

Product Description	Continuous Vinyl Labels are made with UV-stable materials for long outdoor life. The labels are extruded in the actual color and not colored using surface inks for long-term fade resistance. Vinyl labels are provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems. Good for all surface types except powder coat painted or low surface energy substrates such as polypropylene. Test on these surfaces before approving.
---------------------	---

Short Description	Thermal Transfer Adhesive Labels, Solid Color Continuous Roll, 1.0 x 250', UV Stable VL, Yellow, 250 ft/roll
Global Part Name	HT1YE250-1500-YE
Length L (Imperial)	250.0
Length L (Metric)	76.20
Variant	3.2mil, 50lb bleached kraft paper
Width W (Imperial)	1.0
Width W (Metric)	25.4
Thickness T (Metric)	64.0
Width of Liner (Metric)	25.4
Width of Liner (Imperial)	1.0
Material	Type 1500, Vinyl, UV-stabilized, glossy (1500)
Material Shortcut	1500
Adhesive	Acrylic
Halogen Free	No

UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +180°F (-40°C to +82°C)
Operating Temperature	-40°F to +180°F (-40°C to +82°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2014 NEC2011 NEC2020 NEC2017 NEC2023
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	250
Package Quantity (Metric)	76.20
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)