

Specification Sheet

Part Number: 558-00503

Continuous Polyester Labels are made with UV stable materials for long outdoor life.

Labels use UV stable permanent ink.

Continuous polyester is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems.



Adhesive Labels, Solid Color Continuous Roll, 3.0" x 100', UV Stable PET, Red, 100 ft/roll

Article Number	558-00503
Type	HT3RDHB250
Color	Red (RD)
Quantity Per	pack
Product Description	Colored continuous rolls offer a high bond adhesive that is sustainable for low surface energy substrates such as the low density plastics on the front of an inverter or powder coat paint surfaces. The adhesive is designed to adhere to textured surfaces without peeling or falling off.
Short Description	Adhesive Labels, Solid Color Continuous Roll, 3.0" x 100', UV Stable PET, Red, 100 ft/roll

Global Part Name	HT3RDHB250-840/281-RD
Length L (Imperial)	100
Length L (Metric)	30.48
Variant	3.2mil, 50lb bleached kraft paper
Width W (Imperial)	3.0
Width W (Metric)	76.2
Width of Liner (Metric)	76.2
Width of Liner (Imperial)	3.0
Material	Type 840/281, Polyester, UV-stabilized, clear polyester laminate (840/281)
Material Shortcut	840/281
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use

Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 969 NEC2014 CSA 66956 NEC2011 ANSI Standard Z535.4 IFC 2012
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com