

Specification Sheet

Part Number: 175REF

Compact to easily fit in a pocket or on a tool belt.

Dispenser can be reloaded over and over, making it cost effective to use.

Dispenser edge allows easy removal of label liner.

Unlike masking tape, dispenser protects labels from dirt and moisture before use, extending the life and quality of the labels.



Article Number 590-01751

Type RO175REF

Color White (WH)

Quantity Per pack

Product Description HellermannTyton's Rite-On Markers are self laminating wire and cable labels made of flexible vinyl film. A built in clear tail seals the imprint under clear vinyl, maintaining the quality of the messaging and the labels. Rite-On Markers are packaged in a reusable dispenser made from high impact plastic that is resistant to oils and grease.

Short Description Rite-On Self-Laminating Label Refill, 0.75" x .75" x 3.0", VL, White, 90/roll

Global Part Name	RO175REF-100B-WH
------------------	------------------

Fixation Method	Pasting / Stick
-----------------	-----------------

Variant	Roller form
---------	-------------

Width W (Imperial)	0.75
--------------------	------

Width W (Metric)	19.05
------------------	-------

Bundle Diameter Min (Imperial)	0.33
--------------------------------	------

Bundle Diameter Min (Metric)	8.32
------------------------------	------

Bundle Diameter Max (Imperial)	0.33
--------------------------------	------

Bundle Diameter Max (Metric)	8.38
------------------------------	------

Height H (Imperial)	0.75
---------------------	------

Height H (Metric)	19.10
-------------------	-------

Outside Diameter Max (Imperial)	0.7
---------------------------------	-----

Outside Diameter Min (Metric)	8.38
-------------------------------	------

Outside Diameter Min (Imperial)	0.33
---------------------------------	------

Outside Diameter Max (Metric)	17.78
-------------------------------	-------

Material	Type 100B, Vinyl, white transparent, self-laminating (100B)
Material Shortcut	100B
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	No
Adhesive Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	90
Package Quantity (Metric)	90
Customs Number	3919102055

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)