

Specification Sheet

Part Number: 593-11000

No need to change label stock or ribbon colors for each “Warning” type, saving time and reducing inventory.

Unlimited label designs and colors, reducing the need to order custom labels online.

Print icons, images or even full-color photos at 4800 dpi, for professional-looking labels every time.

Print permanent or temporary arc-flash markings as needed for machine and electrical installations to meet NEC and NFPA requirements.

TagPrint Pro 4.0 contains pre-made safety sign templates and images, including GHS signage and pictograms, making label selection easy and fast while ensuring complete ANSI and OSHA code compliance.



Inkjet Printer, 4800 dpi, Beige, 1/pkg

Article Number	593-11000
Type	IJCP1
Color	Beige (BGE)
Quantity Per	pack

Product Description	The HellermannTyton CIJ4800 is a full-color, high-resolution printer for creating photo-quality labels and signs in a single pass. It minimizes material waste as well as needed supplies. The high-yield inkjet cartridge contains high-performance pigment-based inks for maximum resistance to chemicals and solvents. Applications include general or industrial-grade safety signage, GHS, lean/5S and visual workplace identification. The system is easy to use and works with HellermannTyton TagPrint® Pro labeling software.
Short Description	Inkjet Printer, 4800 dpi, Beige, 1/pkg
Global Part Name	IJCP1-PL-BGE
Width W (Imperial)	10.4
Width W (Metric)	264.1
Height H (Imperial)	7.1
Height H (Metric)	180.3
Material	Plastic (PL)
Material Shortcut	PL
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+41°F to +95°F (+5°C to +35°C)

Reach Compliant (Article 33)	No
Certification/Specification	CAGE Code 53421
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8443321040

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com