

Specification Sheet

Part Number: 593-12000

Pigment-based ink rivals consumer-oriented dye-based inks for resistance to chemicals and harsh environments.



Built-in printhead offers a low-maintenance, plug-and-play solution.

Can easily print over 500 full-colored labels (4 x 3") for fewer cartridge changes, which also reduces overall printing costs.

Inkjet Ink Cartridge, Color, Pigment Based, 1/pkg

Article Number 593-12000

Type PBIJC

Color Various (MIX)

Quantity Per pack

Product Description This high-yield ink cartridge is a self-contained, high-resolution inkjet solution for creating photo-quality labels and signs in a single pass, speeding the printing process. High-performance, pigment-based inks provide maximum resistance to chemicals and solvents. The low-maintenance cartridge offers plug-and-play convenience.

Short Description Inkjet Ink Cartridge, Color, Pigment Based, 1/pkg

Global Part Name PBIJC-PL-MIX

Width W (Imperial)	1.0
Width W (Metric)	25.4
Height H (Imperial)	1.625
Height H (Metric)	41.2
Material	Plastic (PL)
Material Shortcut	PL
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+41°F to +95°F (+5°C to +35°C)
Reach Compliant (Article 33)	No
Certification/Specification	CAGE Code 53421
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8443992210

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)