

Specification Sheet

Part Number: TAG50L-105

Laser printable self-laminating polyester has a smooth surface, allowing for the highest resolution and print contrast.

The material is 1.0 mil thick, allowing it to conform around wires and cable.

The acrylic-based adhesive bonds to a wide variety of substrates and can withstand high temperatures long term.

Lasertags are not affected by the high heat required in a laser printer.



Laser Print Label, Self-Laminating, 1.0" x .96" x 3.16", 21 Per Sheet, PET, White, 1000/pkg

Article Number	594-50105
Type	TAG50L
Color	White (WH)
Quantity Per	pack
Product Description	HellermannTyton’s self-laminating labels are used for marking wires and cable. The clear tail overlaps and protects the printed information from abrasion, chemicals and solvents and resists UV exposure. When printed using a laser printer, clear marking and high high-contrast imaging against the wire make this the perfect choice for durable identification.

Short Description	Laser Print Label, Self-Laminating, 1.0" x .96" x 3.16", 21 Per Sheet, PET, White, 1000/pkg
Global Part Name	TAG50L-105-WH
Width W (Imperial)	1.0
Width W (Metric)	25.4
Bundle Diameter Min (Imperial)	0.25
Bundle Diameter Min (Metric)	6.35
Bundle Diameter Max (Imperial)	0.8
Bundle Diameter Max (Metric)	20.20
Thickness T (Metric)	35.0
Width of Liner (Metric)	215.00
Width of Liner (Imperial)	8.5
Outside Diameter Max (Imperial)	0.39
Outside Diameter Min (Metric)	10.1
Outside Diameter Min (Imperial)	0.79
Outside Diameter Max (Metric)	20.20

Material	Type 105, Polyester, white (105)
Material Shortcut	105
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3919905060
Labels per Column	3
Labels per Row	8

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)