


Specification Sheet

Part Number: TAG53L-788



White polyester has a smooth surface, allowing for the highest resolution and print contrast.

The acrylic-based adhesive bonds to a wide variety of substrates and resists abrasion.

LaserTags are sheet fed for easy loading and fast printing.

Laser Tag Label, 8.5" x 11", 1 Per Sheet, PET, White, 250/pkg

Article Number	594-53788
Type	TAG53L
Color	White (WH)
Quantity Per	pack
Product Description	HellermannTyton white polyester labels are ideal for marking small electrical and electronic components, such as EPROMS', Integrated circuits, as well as the circuit board itself. Printed labels can withstand the soldering process and survive flux removal when the board is washed. HellermannTyton's 788 material is designed for use on flat surfaces and can also be used to identify connectors, buttons and just about anything requiring permanent, general purpose marking.
Short Description	Laser Tag Label, 8.5" x 11", 1 Per Sheet, PET, White, 250/pkg

Global Part Name	TAG53L-788-WH
Width W (Imperial)	8.5
Width W (Metric)	215.9
Bundle Diameter Min (Imperial)	0.24
Bundle Diameter Min (Metric)	6.10
Thickness T (Metric)	64.0
Height H (Imperial)	10.81
Height H (Metric)	274.60
Material	Type 788, Polyethylene Terephthalate (788)
Material Shortcut	788
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-40°F to +199°F (-40°C to +93°C)

Operating Temperature	-40°F to +199°F (-40°C to +93°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	250
Package Quantity (Metric)	250
Customs Number	3919905060
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com