

Specification Sheet

Part Number: TAG22-100

- Dot matrix printable self-laminating vinyl has a smooth surface, allowing for the highest resolution and print contrast using an impact printer.
- The material is a conformable vinyl, allowing it to wrap and stay around wires and cable.
- The acrylic-based adhesive bonds to a wide variety of substrates and will remain in place long term.
- Tabtag dot matrix labels are specifically made for use in dot matrix printers for fast and easy printing.
- Labels come with a pin-feed margin to ensure that they can easily be loaded into any dot matrix printing system.



Dot Matrix Label, Self-Laminating, 1.0 x 0.50 x 1.43", 8 Across, VL, White, 5000/pkg

Article Number	595-22100
Type	TAG22
Color	White (WH) Clear (CL)
Quantity Per	pack

Product Description	HellermannTyton's self-laminating labels are used for marking wires and cable. The clear tail overlaps and protects the printed information from abrasion, chemicals and solvents and resists UV exposure. When printed using any standard dot matrix printer, clear marking and high high-contrast imaging against the wire make this the perfect choice for durable identification.
Short Description	Dot Matrix Label, Self-Laminating, 1.0 x 0.50 x 1.43", 8 Across, VL, White, 5000/pkg
Global Part Name	TAG22-100B-CL/WH
Fixation Method	Pasting / Stick
Variant	Adhesive label
Width W (Imperial)	1.0
Width W (Metric)	25.4
Bundle Diameter Min (Imperial)	0.12
Bundle Diameter Min (Metric)	3.04
Bundle Diameter Max (Imperial)	0.25
Bundle Diameter Max (Metric)	6.35
Thickness T (Metric)	75.0
Width of Liner (Metric)	228.60
Width of Liner (Imperial)	8.9

Outside Diameter Max (Imperial)	0.29
Outside Diameter Min (Metric)	3.8
Outside Diameter Min (Imperial)	0.14
Outside Diameter Max (Metric)	7.60
Material	Type 100B, Vinyl, white transparent, self-laminating (100B)
Material Shortcut	100B
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-51°F to +200°F (-46°C to +93°C)
Operating Temperature	-51°F to +200°F (-46°C to +93°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-Recognized

UL Recognized (US)	Yes
Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3919905060
Labels per Column	8
Labels per Row	8

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)