

Specification Sheet

Part Number: 596-00252

Made with UV-stable inks and materials for durability and weather resistance.

Reflective properties to meet applicable NEC® code requirements for reflective identification.

Supplied with an aggressive adhesive to ensure long life.

NOMINAL OPERATING AC VOLTAGE	
NOMINAL OPERATING AC FREQUENCY	
MAXIMUM AC POWER	
MAXIMUM AC CURRENT	
MAX OVERCURRENT DEVICE RATING	
FOR AC MODULE PROTECTION	

Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

Solar Label, Printable, AC MODULE, 4.0" x 2.0", PET, Red, 50/roll

Article Number	596-00252
Type	AC2011
Color	Red (RD)
Quantity Per	pack
Product Description	Designed with cross-laminated UV stable materials, these variable print Solar Installation Labels are designed to accept printing from any standard thermal transfer printer using a resin-based ink ribbon for the best durability. Print your voltage information directly on the label and then laminate with an optional clear acrylic laminate material for added protection. These labels can be used to print disconnecting means and breaker series directly on the labels for a more professional result and a smoother inspection process.

Short Description	Solar Label, Printable, AC MODULE, 4.0" x 2.0", PET, Red, 50/roll
Global Part Name	AC2011-840/281-RD
Local Order Number 2	Cross Reference = 10 per pack: 596-00255; Printable Metal Solar Placard 5 pack: 596-00840; Engravable Metal Solar Placard 5 pack: 596-00863; Spanish version 50 per roll: 596-00816
Width W (Imperial)	4.0
Width W (Metric)	101.6
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	2.0
Height H (Metric)	50.8
Material	Type 840/281, Polyester, UV-stabilized, clear polyester laminate (840/281)
Material Shortcut	840/281
Adhesive	Acrylic
Halogen Free	Yes
UV Resistant (Yes/No)	Yes

Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 969 NEC2017 NEC2014 CSA 66956 IFC 2012
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com