

Specification Sheet

Part Number: 596-00383

Thermal transfer labels are made with high-performance materials for long-term industrial applications.

Labels can be printed in any standard thermal transfer printer giving the user options for printing and eliminating the need to be dedicated to one printer model.

The labels are available in a wide variety of sizes so that finding a label for a particular application is easy.



Phase label, 1" x .5", PET, Black, 2500/roll

Article Number	596-00383
Type	PLB3P
Color	Black (BK)
Quantity Per	pack
Product Description	Phase labels are microperforated between each label so that it can be applied as one strip to the panel or broken into individual labels.
Short Description	Phase label, 1" x .5", PET, Black, 2500/roll
Global Part Name	PLB3P-PET-BK

Local Order Number 2 596-00383

Width W (Imperial) 1.0

Width W (Metric) 25.4

Thickness T (Metric) 64.0

Height H (Imperial) 0.5

Height H (Metric) 12.7

Width of Liner (Metric) 85.09

Width of Liner (Imperial) 3.35

Material Polyester (PET)

Material Shortcut PET

Adhesive Acrylic

Halogen Free No

UV Resistant (Yes/No) No

Use Conditions For Indoor Use Only

Operating Temperature -40°F to +300°F (-40°C to +149°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

UL Recognized (US) Yes

Package Quantity (Imperial) 2500

Package Quantity (Metric) 2500

Customs Number 3919102055

Labels per Column 3

Labels per Row 3

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)