

Specification Sheet

Part Number: 596-00648

Preprinted Solar Labels are made with UV-stable inks and materials for durability, weather resistance and long-term outdoor use.

Polyester is resistant to chemicals and solvents and will remain legible in dirty environments.



High abrasion and scuff resistance for high performance labeling.

Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

Pre-Printed Header Label, DANGER, 3.0 x 2.0", UV Stable PET, Red, 250/roll

Article Number

596-00648

Type

3X2DANGERUV

Color

Red (RD)

Quantity Per

pack

Product Description

These labels come with preprinted color headers so only one color of ribbon is needed to complete the message panel. Labels can be used with TagPrint® Pro label software and HellermannTyton thermal transfer printers to reduce labor, eliminate minimum orders and allow the user to create labels on demand.

Short Description	Pre-Printed Header Label, DANGER, 3.0 x 2.0", UV Stable PET, Red, 250/roll
Global Part Name	3X2DANGERUV-336/926-RD
Width W (Imperial)	3.0
Width W (Metric)	76.20
Thickness T (Metric)	64.0
Height H (Imperial)	2.0
Height H (Metric)	50.80
Width of Liner (Metric)	81.28
Width of Liner (Imperial)	3.2
Material	Type 336/926, Polyester, UV stabilized, clear polyester laminate (336/926)
Material Shortcut	336/926
Adhesive	Acrylic
Halogen Free	Yes
UV Resistant (Yes/No)	Yes

Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2014 CSA 66956 NEC2011 NEC2020 IFC 2012 UL 969 NEC2017 ANSI Standard Z535.4
UL Recognized (US)	Yes
Package Quantity (Imperial)	250
Package Quantity (Metric)	250
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com