

Specification Sheet


Part Number: 596-00678

Made with UV-stable inks and materials for durability and weather resistance.

Polyester is resistant to chemicals and solvents and will remain legible in dirty environments.

Abrasion resistant for high-performance identification.

Meets NEC and IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.



Solar Label, Reflective, Warning Photovoltaic Power Source, 6.5" x 1.0", VL, Red, 10/pkg

Article Number	596-00678
Type	PVPSR10
Color	Red (RD)
Quantity Per	pack

Product Description	HellermannTyton makes it easier than ever for solar installers to meet PV labeling codes. Solar Label Convenience Packs allow installers to quickly and economically purchase high quality preprinted NEC code-compliant solar installation labels. Packaged in 10-count quantities to meet the needs of smaller scale solar installations and independent contractors, Solar Label Convenience Packs are available in HellermannTyton's most popular preprinted NEC code-compliant solar label formats. Each Solar Label Convenience Pack contains 10 solar installation labels. Choose from a variety of regular and reflective preprinted labels. For enhanced durability, clear laminate overlay labels are also available in a convenience pack.
Short Description	Solar Label, Reflective, Warning Photovoltaic Power Source, 6.5" x 1.0", VL, Red, 10/pkg
Global Part Name	PVPSR10-505/281-RD
Local Order Number 2	Cross Reference = 50 per roll: 596-00206
Width W (Imperial)	6.5
Width W (Metric)	165.1
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	1.0
Height H (Metric)	25.40
Width of Liner (Metric)	28.57
Width of Liner (Imperial)	1.125

Material	Type 505/281, UV stabilized, reflective vinyl with clear polyester laminate (505/281)
Material Shortcut	505/281
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2017 UL 969 NEC2014
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10

Customs Number	3919905060
----------------	------------

Labels per Column	1
-------------------	---

Labels per Row	1
----------------	---

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)