

Specification Sheet

Part Number: 596-00737

Made with UV stable inks and materials for durability and weather resistance.

The labels are supplied with aggressive adhesive to ensure long life.

**PHOTOVOLTAIC SYSTEM
kWh METER**

Solar Installation labels meet NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

Solar Label, PHOTOVOLTAIC SYSTEM kWh METER, 4.0" x 1.0", VL, Red, 50/roll

Article Number 596-00737

Type PSKWH

Color Red (RD)

Quantity Per pack

Product Description Many times common solar label designs are specified even though they might not be required by code. HellermannTyton offers a selection of some of the most commonly requested labels for use on solar installations.

Short Description Solar Label, PHOTOVOLTAIC SYSTEM kWh METER, 4.0" x 1.0", VL, Red, 50/roll

Global Part Name PSKWH-V-RD

Width W (Imperial)	4.0
Width W (Metric)	101.6
Height H (Imperial)	1.0
Height H (Metric)	25.40
Material	Vinyl (V)
Material Shortcut	V
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2014 NEC2020 NEC2011 NEC2017

Warranty (US) Yes

UL Recognized (US) Yes

Package Quantity (Imperial) 50

Package Quantity (Metric) 50

Customs Number 3919102055

Labels per Column 1

Labels per Row 1

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)