

Specification Sheet

Part Number: CMFO4

Markers are pre-coiled so that they can be snapped into place over the cable without the use of adhesives.

Non-adhesive design means that the markers can be installed at any temperature or over dirty or oily surfaces.



Pre-printed text is protected by a thick layer of clear acrylic which provides UV protection and abrasion resistance.

Fiber Optic Cable Marker, Coiled, 4.0" x 4.0", VL, Orange, 25/pkg

Article Number	597-00042
Type	CMF
Color	White (WH)
Quantity Per	pack
Product Description	HellermannTyton's coiled markers are made from heavy duty vinyl and come pre-printed with a standard warning. Custom printing is available - please call for more information.
Short Description	Fiber Optic Cable Marker, Coiled, 4.0" x 4.0", VL, Orange, 25/pkg
Global Part Name	CMF-V-WH

Length L (Imperial)	5.0
Length L (Metric)	127.00
Width W (Imperial)	4.0
Width W (Metric)	101.60
Height H (Imperial)	3.0
Height H (Metric)	76.20
Outside Diameter Max (Imperial)	0.75
Outside Diameter Min (Metric)	12.7
Outside Diameter Min (Imperial)	0.5
Outside Diameter Max (Metric)	19.01
Material	Vinyl (V)
Material Shortcut	V
Halogen Free	No
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use

Operating Temperature -18°F to +200°F (-29°C to +93°C)

Reach Compliant (Article 33) No

ROHS Compliant Yes

Package Quantity (Imperial) 25

Package Quantity (Metric) 25

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)