

Specification Sheet

Part Number: GT.375X60C2



Features quick release for repetitive access to cable and wire.

Can be opened and closed numerous times without failure.

Adjustable so one size can accommodate multiple bundle sizes.

Grip Tie Strap, 6.0" x .38", PA6/PP, Black, 100/pkg

Article Number	854-44316
Type	GT.375X6
Color	Black (BK)
Quantity Per	pack
Product Description	The Grip Tie is a low-profile, one-piece fastening device. Constructed of a hook and loop design, laminated back to back, the Grip Tie features quick release for repetitive access to cable and wire. Reusable, adjustable, releasable, and easy to install, it can be successfully opened and closed numerous times. Grip Ties are available in a variety of colors and are versatile enough for applications ranging from network installations to bundling power cords.
Short Description	Grip Tie Strap, 6.0" x .38", PA6/PP, Black, 100/pkg

Global Part Name	GT.375X6
Minimum Tensile Strength (Imperial)	40
Minimum Tensile Strength (Metric)	177.93
Length L (Imperial)	6.0
Length L (Metric)	152.4
Width W (Imperial)	0.375
Width W (Metric)	9.525
Bundle Diameter Max (Imperial)	1
Bundle Diameter Max (Metric)	25.4
Material	Polyamide 6 (PA6) Polyethylene (PE)
Material Shortcut	PE PA6
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Reach Compliant (Article 33)	No

Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)