

Specification Sheet

Part Number: 904-00357

Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install.

Tubing provides full coverage where spiral wrap or other coverings may not be suitable.

In harsh applications the tubing provides resistance to crushing, impact, and abrasion.

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.



Convoluted Tubing, Slit, 1.5" Dia, PEUV, Black with Orange Stripe, 1000ft/carton

Article Number 904-00357

Type CTPUV1120

Color Black with Orange Stripe (BKSTOG)

Quantity Per pack

Product Description

HellermannTyton's Convoluted Tubing, also known at Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offer's excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.

Short Description

Convoluted Tubing, Slit, 1.5" Dia, PEUV, Black with Orange Stripe, 1000ft/carton

Global Part Name

CTPUV1120-PEUV-BK

Length L (Imperial)

1000.0

Length L (Metric)

304.8

Variant

Slit

Bundle Diameter Min (Imperial)

0.1

Bundle Diameter Min (Metric)

1.0

Bundle Diameter Max (Imperial)

1.64

Bundle Diameter Max (Metric)

41.8

Inner Diameter D (Imperial)

1.647

Inner Diameter D (Metric)

41.83

Diameter D (Imperial)

1.947

Diameter D (Metric)	49.45
Outside Diameter OD (Imperial)	1.947
Outside Diameter OD (Metric)	49.45
Nominal Diameter (Imperial)	1.5
Nominal Diameter (Metric)	38.1
Wall Thickness WT (Imperial)	0.006
Wall Thickness WT (Metric)	0.152
Material	Polyethylene, UV-resistant (PEUV)
Material Shortcut	PEUV
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial) 1000

Package Quantity (Metric) 304.80

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)