

## Specification Sheet

Part Number: 904-00358

Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install.

Tubing provides full coverage where spiral wrap or other coverings may not be suitable.

In harsh applications the tubing provides resistance to crushing, impact, and abrasion.

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.



Convoluted Tubing, Slit, 0.75" Dia, PEUV, Black with Orange Stripe, 4200ft/carton

Article Number 904-00358

Type CTPUV340

Color Black with Orange Stripe (BKSTOG)

Quantity Per pack

**Product Description**

HellermannTyton's Convoluted Tubing, also known at Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offer's excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.

**Short Description**

Convoluted Tubing, Slit, 0.75" Dia, PEUV, Black with Orange Stripe, 4200ft/carton

**Global Part Name**

CTPUV340-PEUV-BK

Length L (Imperial)

4200.0

Length L (Metric)

1280.2

Variant

Slit

Bundle Diameter Min (Imperial)

0.1

Bundle Diameter Min (Metric)

1.0

Bundle Diameter Max (Imperial)

0.75

Bundle Diameter Max (Metric)

19.3

Inner Diameter D (Imperial)

0.759

Inner Diameter D (Metric)

19.28

Diameter D (Imperial)

0.989

Diameter D (Metric)	25.12
Outside Diameter OD (Imperial)	0.989
Outside Diameter OD (Metric)	25.12
Nominal Diameter (Imperial)	0.75
Nominal Diameter (Metric)	19.05
Wall Thickness WT (Imperial)	0.005
Wall Thickness WT (Metric)	0.127
Material	Polyethylene, UV-resistant (PEUV)
Material Shortcut	PEUV
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial) 4200

Package Quantity (Metric) 1280.20

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)