


Solar Edge Clips

Features and Benefits

- Integrated design allows for easy insertion by hand
- Rounded edges protect the cable insulation from damage
- Double-compression design that accommodates up to two cables and various sizes (4-6 mm²)
- High extraction force for withstanding extreme conditions
- Made from SS304 stainless steel



Material	Stainless Steel (SS304)
Color	Metal (ML)
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Certifications	E64139 [cRUs], E64139 [cULus]



PART NO.	TYPE	Panel Thickness in. (mm)	Min. Cable Diameter in. (mm)	Max. Cable Diameter in. (mm)	Length (L) in. (mm)	Width (W) in. (mm)	Pkg. Qty.
151-00982*	MSC2	0 - 0.1 (1 - 3)	0.20 (5.0)	0.30 (7.6)	0.95 (24.1)	0.50 (13.0)	100
151-02320*		0 - 0.1 (1 - 3)	0.20 (5.0)	0.30 (7.6)	0.95 (24.1)	0.50 (13.0)	5000

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

Contact HellermannTyton for more information.

Visit www.hellermann.tyton.com or call 800.537.1512

Disclaimer: The information in this datasheet is for informational purposes only. Information is subject to change at any time without notice.

HellermannTyton