

TECHNICAL DATA SHEET

Part No. T30RA30
Article No. 103-00002
Type T30RA



Cable ties for use with HellermannTyton's AT2060 automatic cable tie tool

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	600
Carton Qty.	6000
Customs Number	3926909988

Releasable Closure	No
Length (imperial)	6.0 "
Length (metric)	152.4 mm
Max. Bundle Diameter (imperial)	1.25 "
Max. Bundle Diameter (metric)	31.75 mm
Min. Bundle Diameter (imperial)	0.06 "
Min. Bundle Diameter (metric)	1.5 mm
Min. Tensile Strength (imperial)	30 lbs
Min. Tensile Strength (metric)	135 N
Reel Diameter	450.0 mm
Reel Diameter (imperial)	17.7 "
Reel Width	182.8 mm
Reel Width (imperial)	7.197 "
Width (imperial)	0.14 "
Width (metric)	3.6 mm

