

TECHNICAL DATA SHEET

Part No. 104-10000
Article No. 104-10000
Type ProCut 9



The ProCut battery powered cable tie tool system automatically tensions and cuts T50-T250 and wide strap cable ties. A single pull of the trigger does all the work. Its 16 tension settings ensure precision results. Designed for professionals with an ergonomic, soft-grip handle and low-force trigger to reduce hand strain. A secondary trigger button on the rear assists in hard-to-reach applications. The ProCut can produce up to 2,000 cycles per charge utilizing the Metabo CAS battery (also used on our CPK Hybrid tool).

Material	Metal (MET), Plastic (PL)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Blue (BU)
Pkg. Qty.	1
Carton Qty.	1
Customs Number	8467290095

Power Supply	CAS Lithium-Ion Battery
Description	ProCut 9 with battery and charger
For Cable Tie Series	T50 - T250
For Cable Tie Width (metric)	4.6 - 13.5 mm
Max. Cable Tie Thickness (imperial)	0.08 "
Max. Cable Tie Thickness (metric)	2.0 mm
Operation	electrical
Tension Setting	Adjustable

RoHS ✓