

TECHNICAL DATA SHEET

Part No. 110-77003
Article No. 110-77003
Type EVO7i



HellermannTyton's EVO 7i industrial-grade, mechanical hand tool is ergonomically designed to reduce the risks of repetitive stress injuries to operators while simultaneously increasing productivity. The EVO 7i's Tension/ Lock/Cut Technology delivers performance, safety and comfort for operators. Calibrated tensioning assures consistent wire bundle tension before flush cut-off. Available in a standard grip span (EVO 7i) or short grip span (EVO 7iSP) for smaller hands. Additional accessories are available.

Material	Metal (MET), Plastic (PL)
Use Conditions	For Indoor Use Only
Color	Blue (BU), Black (BK)
Pkg. Qty.	1
Carton Qty.	20 EA
Customs Number	8205599000

Description	EVO 7i Mechanical Hand Tool, Standard Hand Span
For Cable Tie Series	T18, T30, T40, T50, T80, IT18, IT50
For Cable Tie Width (metric)	2.5 - 4.8 mm
Height (imperial)	5.4 "
Height (metric)	137.3 mm
Length (imperial)	7.5 "
Length (metric)	191.0 mm
Max. Cable Tie Thickness (imperial)	0.06 "
Max. Cable Tie Thickness (metric)	1.5 mm
Operation	manual
Tension Setting	Adjustable
Width (imperial)	1.3 "
Width (metric)	34.2 mm

