

TECHNICAL DATA SHEET

Part No. 110-77004
Article No. 110-77004
Type EVO7iSP



HellermannTyton's EVO 7i industrial-grade, mechanical hand tool is ergonomically designed to reduce the risks of repetitive stress injuries to operators while simultaneously increasing productivity. The EVO 7i's Tension/Lock/Cut Technology delivers performance, safety and comfort for operators. Calibrated tensioning assures consistent wire bundle tension before flush cut-off. Available in a standard grip span (EVO 7i) or short grip span (EVO 7iSP) for smaller hands. Additional accessories are available.

Material	Metal (MET), Plastic (PL)
Use Conditions	For Indoor Use Only
Color	Blue (BU), Black (BK)
Pkg. Qty.	1
Carton Qty.	20 EA
Customs Number	8205599000

Description	EVO 7iSP Mechanical Hand Tool, Short Hand Span
For Cable Tie Series	T18, T30, T40, T50, T80, IT18, IT50
For Cable Tie Width (metric)	2.5 - 4.8 mm
Length (imperial)	7.5 "
Length (metric)	192 mm
Operation	manual
Tension Setting	Adjustable

