

TECHNICAL DATA SHEET

Part No. 110-80004
Article No. 110-80004
Type EVO9HT



HellermannTyton's EVO 9 manual cable tie application tool combines durability, precision and control with unparalleled comfort. Manufactured with high-performance materials and components, the EVO 9 cuts cable ties with up to 250-lb tensile strength. Its innovative, ergonomic design minimizes the stress on hands and wrists and "kickback" that occur with traditional tools, reducing the risk of repetitive-motion injuries. The HT model offers high tension while the SP model features a smaller grip.

Material	Metal (MET), Plastic (PL)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Red (RD), Black (BK)
Pkg. Qty.	1
Carton Qty.	20
Customs Number	8205599000

Description	EVO 9HT High Tension Mechanical Hand Tool
For Cable Tie Series	T120, T150, T250, T255, WS
For Cable Tie Width (metric)	4.6-13.5 mm
Height (imperial)	5.3 "
Height (metric)	135 mm
Length (imperial)	7.5 "
Length (metric)	191 mm
Max. Cable Tie Thickness (imperial)	0.08 "
Max. Cable Tie Thickness (metric)	2.0 mm
Operation	manual
Width (imperial)	1.3 "
Width (metric)	33 mm

RoHS